


ERA

Maxim Tilt Safe Window Handle Operation Instructions

180°
Turn / Unlock



3

To reinstate Tilt Safe mode, rotate the handle to between 0° -90° and repeat Step 1.

2

Release the button by rotating the key. Handle is now free to move past 90° in Turn mode.

90°

Tilt (Ventilation) /
Locked (Tilt Safe mode)

1

Insert and rotate key to restrict to Tilt mode (button depressed). Handle will now operate in Tilt Safe mode only (handle can turn 90° in either direction).

Please note: the handle should be installed with the 'TS' (under the cover cap) as the top hole position for the handle to operate correctly. If you rotate the handle past 90° and use the key to depress the button, you can lock the handle in Turn mode (not recommended). To unlock, release the button using the key.